

MRDS QUICK REFERENCE CARD SERIES



Holosun EPS/Carry Red MRS

Power ON: Shake or press either brightness button

Power OFF: Press "+" and "-" together

Press "+" 3 sec to go from Automatic(*) -> Manual -> Lockout
Solar Fail Safe™ provides dual power (solar and internal)


Automatic Brightness dims down to adjust for ambient light
12 brightness settings (4 NV, 8 daylight)

*default

GENERAL PURPOSE GRID: 1.00"

Layout / Design llando88@gmail.com 2022. Unlimited copy and distribution permitted. **REV 10**

Holosun EPS/Carry Red MRS



Battery is **CR1620 3V**. Reticle blinks if battery is low.

Insert new battery "+" side **DOWN**

Screws move center of impact U/D, R/L. 1 Click = 1.5 MOA

25 yds: 2 MOA = 0.5" **10 yds:** 2 MOA = 0.2"

Optic screws: T10 6-32x5/16": 15 in-lbs + blue threadlocker

Tray screw : M2x0.4

Clean with lens cleaner, **NO** alcohol or acetone

Footprint: Holosun "K" Series / 7075 T6 AL / IPX8 Certified

www.holosun.com warranty@holosun.com (909) 594-2888

ZEROING AID GRID: 2 MOA@25 YD±0.52"

Instructions: Cut on dotted lines / fold to make a 3x5 "card". Information adapted from OEM sources; not verified nor endorsed. User is advised to verify any content herein with manufacturers documentation.

MRDS QUICK REFERENCE CARD SERIES



Holosun EPS/Carry Red MRS

Power ON: Shake or press either brightness button

Power OFF: Press "+" and "-" together

Press "+" 3 sec to go from Automatic(*) -> Manual -> Lockout
Solar Fail Safe™ provides dual power (solar and internal)

Automatic Brightness dims down to adjust for ambient light
12 brightness settings (4 NV, 8 daylight)

*default

GENERAL PURPOSE GRID: 1.00"

Layout / Design llando88@gmail.com 2022. Unlimited copy and distribution permitted. **REV 10**

Holosun EPS/Carry Red MRS



Battery is **CR1620 3V**. Reticle blinks if battery is low.

Insert new battery "+" side **DOWN**

Screws move center of impact U/D, R/L. 1 Click = 1.5 MOA

25 yds: 2 MOA = 0.5" **10 yds:** 2 MOA = 0.2"

Optic screws: T10 6-32x5/16": 15 in-lbs + blue threadlocker

Tray screw : M2x0.4

Clean with lens cleaner, **NO** alcohol or acetone

Footprint: Holosun "K" Series / 7075 T6 AL / IPX8 Certified

www.holosun.com warranty@holosun.com (909) 594-2888

ZEROING AID GRID: 2 MOA@25 YD±0.52"

Instructions: Cut on dotted lines / fold to make a 3x5 "card". Information adapted from OEM sources; not verified nor endorsed. User is advised to verify any content herein with manufacturers documentation.